





1X6PIN



1X8PIN



1X7PIN



1X9PIN



1X5PIN



1X10 PIN



1X4PIN



1X11PIN



1X3PIN



1X12PIN



1X2PIN

Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 5A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -40°C~+105°C
- Insulation resistance: $\geq 1000M \Omega$
- Contact resistance: $\leq 10m \Omega$
- After environmental testing : $\leq 20m \Omega$

X3025 H F-02I-N2

① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No.
② Category : H-HSG
③ Welding Board Angle : F-Female HSG
④ Row No.-Pin No.: XX-02P~12P
⑤ Plug the Pin & special No. : I-Without Ears
G-With Ears
⑥ Material : N2-PA66 94 V-2;
⑦ Color: Blank -Natural Color ; WH-White

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
02	3.00	6.90	08	21.00	24.90
03	6.00	9.90	09	24.00	27.90
04	9.00	12.90	10	27.00	30.90
05	12.00	15.90	11	30.00	33.90
06	15.00	18.90	12	33.00	36.90
07	18.00	21.90			

X3025HF-02G-N2	Nylon 66 94V-2	Natural Color	X3025TM	X3025HM	With Ears
X3025HF-02G-N2WH	Nylon 66 94V-2	White			
X3025HF-02I-N2	Nylon 66 94V-2	Natural Color	X3025TM	X3025HM	Without Ears
X3025HF-02I-N2	Nylon 66 94V-2	White			
PART NO	Material	Color	Suitable XKB Terminal	Mates With XKB Housing	Note

							DSND		DATE		SCALE: N/A	MODEL TYPE: 3.00 mm Crimp Style Connectors		
Δx				XKB	ANGLAR	±5°	DWN		DATE		VIEW: 	PART NO.: X3025HF-02I-N2		
Δx					4<L≤16	±0.3	CHKD		DATE		UNIT: mm/in	X3025HF-02I-N2		
Δx					16<L≤63	±0.4	APPD		DATE		SIZE: A4			
MARK	DESCRIPTION			DATE	REVISED	APPROVED						L>63	±0.5	X-X3025HF-02I-N2
REVISIONS							UNSPECIFIED TOLERANCES							
www.helloxkb.com							XKB INDUSTRIAL PRECISION CO.,LIMITED							
												WEIGHT 1.0g	SHEET 1/1	REVISION A0