







	REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.05.22	阿树



NUMBER OF POSITIONS	DIMENSION				
	A±0.40	B±0.30	C±0.30	D±0.25	E±0.25
9	30.80	25.00	16.35	11.08	10.10
15	39.14	33.30	24.75	19.39	17.70
25	53.05	47.04	38.35	33.24	30.30
37	69.32	63.50	54.75	49.86	45.70

X07XXFXXX3	XDBLS	XDBLM
PART NO	SCREW	NUT

PART NO.:

①Series NO.
②Row No.Pin No.XX-09;15;25;37
③Welding Board Angle :F-Female
④T: Tradtional C: Car-pin
⑤Planting Category: 1:1U' 2:2U' 3:3U' 4:5U'
5:15U' 6:30U' 7:AU Sn
⑥Color:B-BLACK W-White BL-Blue
⑦3:TYPE-3;

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE: D-SUB
CHECKED		UNIT: mm/in		PART NO.: X0725FT7B3
APPROVED		SIZE: A4		DWG NO.: X-X0725FT7B3
PRECISION CO., LIMITED				SCALE
				PAGE
				REVISION
				N/A
				1/1
				A1