





REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		图面升级整理图面	2025.02.26	阿树
A2	N/A		产品电气性能变更	2025.12.23	阿树



X4621WRS-2xXXIS-C40D64


X4621WRS-2xXXI-C40D64

Specifications:
规格:
Voltage rating:500V AC/DC
额定电压: 500V AC/DC
Current rating:2A AC/DC
额定电流: 2A AC/DC
Withstanding voltage:500V AC/minute
耐受电压: 500V AC/分钟
Temperature range:-40℃~+125℃
温度范围: -40℃~+125℃
Insulation resistance:1000MΩ min
绝缘电阻: 1000MΩ Min
Contact resistance:20MΩ Max
接触电阻: 20MΩ Max
Plating Category:1U'' Gold
镀层:1U'' Gold
Reflow soldering temperature:260±5℃, 10S
回流焊温度: 260±5℃, 10S

PART NO.:

X4621 W R S-2x03 I-C40 D64
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ①Series No
②Category:W-Wafer
③Welding Board Angle:R-Stright 90°
④Welding Way:S-SMT
⑤Row No.Pin No:2xXX Pin
⑥Plastic Height:l=2.0mm
⑦Pin length:C=4.0mm
⑧Pin length:D=6.4mm



AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE: 2.0mm BTB Connector
CHECKED		UNIT: mm/in	PART NO.: X4621WRS-2x03I-C40D64
APPROVED		SIZE: A4	DWG NO.: X-X4621WRS-2x03I-C40D64

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A2