

1

2

3

4

A

B

C


D

A






B

C

D



SCALE:1/2



REVISIONS

REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.9.06	阿树

■SPECIFICATIONS

- Voltage rating:250V AC/DC
- Current rating:3A AC/DC
- Withstanding Voltage:1000V AC/minute
- Temperature range:-40°C~+125°C
- Insulation resistance:≥500MΩ
- Contact resistance:≤20mΩ

PART NO.:

X1511 H-14 L-N0
① ② ③ ④ ⑤

- ①Series No
②Category:H-HSG
③Row No.Pin No:XX-02~15P
④Special N0:L-With Lock
⑤Material:N0-Nylon 66 UL94V-0

Poles	Dimensions(mm)		
	A	B	C
02	1.50	4.10	3.30
03	3.00	5.60	4.80
04	4.50	7.10	6.30
05	6.00	8.60	7.80
06	7.50	10.10	9.30
07	9.00	11.60	10.80
08	10.50	13.10	12.30
09	12.00	14.60	13.80
10	13.50	16.10	15.30
11	15.00	17.60	16.80
12	16.50	19.10	18.30
13	18.00	20.60	19.80
14	19.50	22.10	21.30
15	21.00	23.60	22.80

X1511H-14L-N0	PA66	X1511W-L	X1511L-T
PART NO	Material	Suitable XKB Wafer	Suitable XKB Terminal

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE: 1.50mm Crimp Style Connectors
CHECKED		UNIT: mm/in	PART NO.: X1511H-14L-N0
APPROVED		SIZE: A4	DWG NO.: X-X1511H-14L-N0

1

2

3

4