





| REVISIONS |         |          |                 |           |        |
|-----------|---------|----------|-----------------|-----------|--------|
| REV.      | ECN NO. | LOCATION | DESCRIPTION     | DATE      | DESIGN |
| A0        | N/A     |          | INITIAL RELEASE | /         | /      |
| A1        | N/A     |          | 图面升级整理图面        | 2025.2.27 | 阿树     |



规格 Specifications:

额定电压 Voltage rating:250VAC/DC.

额定电流 Current rating:1A AC/DC

耐电压 Withstanding voltage:300V AC/minute

温度区间 Temperature range:-40℃to+105℃

绝缘电阻 Insulation resistance:≥500MΩ Min

接触电阻 Contact resistance:≤20MΩ Max

材料 Material: PA6T 94V-0

镀层 Plating Category: 1U"Gold

波峰焊温度 Wave soldering temperature:255±5℃,10s

PART NO.:

X1311 W V-39 J-C18 D27

① ② ③ ④ ⑤ ⑥ ⑦

- ①Series No
- ②Category:W-Water
- ③Welding Board Angle:V-Straight 180°
- ④Row No -Pin No:XX-01P-40P
- ⑤Plastic height: J=1.0mm
- ⑥Plastic length:C=2.7mm
- ⑦Plastic length:D=1.8mm

|                    |            |               |             |                     |
|--------------------|------------|---------------|-------------|---------------------|
| X1311WV-39J-C18D27 | PA6T 94V-0 | Brass         | 1U"Gold     | X1311F              |
| PART NO            | Material   | Material(Pin) | Finish(Pin) | Suitable XKB Female |

|                        |       |
|------------------------|-------|
| AuGLAR                 | ±5°   |
| X.                     | ±0.40 |
| X.x                    | ±0.30 |
| X.xx                   | ±0.20 |
| X.xxx                  | ±0.15 |
| UNSPECIFIED TOLERANCES |       |



|          |    |             |                                  |
|----------|----|-------------|----------------------------------|
| DESIGN   | 阿树 | VIEW:       | MODEL TYPE: 1.27mm BTB Connector |
| CHECKED  |    | UNIT: mm/in | PART NO.: X1311WV-39J-C18D27     |
| APPROVED |    | SIZE: A4    | DWG NO.: X-X1311WV-39J-C18D27    |
| SCALE    |    |             | PAGE                             |
| N/A      |    |             | 1/1                              |
| REVISION |    |             | A1                               |