







REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.12.18	阿树



- Specifications (规格):
- 1.Voltage rating(额定电压):DC 30V
 - 2.Current rating(额定电流):0.5A AC/DC
 - 3.Withstanding voltage(耐压值): $\geq 500V$ AC/minute
 - 4.Insulation resistance(绝缘电阻): $\geq 100M\Omega$ Min
 - 5.Contact resistance(接触电阻): $\leq 30m\Omega$ Max
 - 6.Mating cycles (使用寿命): 5000 cycles Min
 - 7.Insertion and extraction force (插拔力): 3~20N

7	terminal 6	Phosphor Bronze	Black
6	terminal 5	Phosphor Bronze	tin
5	terminal 4	Brass	tin
4	terminal 3	Brass	tin
3	terminal 2	Phosphor Bronze	tin
2	terminal 1	Phosphor Bronze	tin
1	Pedestal	PBT	
N0	Name	Material	Remarks

DESIGN	阿树	VIEW:	MODEL TYPE: 3.5 PHONE JACK
CHECKED		UNIT: mm/in	PART NO.: PJ-3282-B-SMT
APPROVED		SIZE: A4	DWG NO.:
SCALE			PAGE
N/A			1/1
REVISION			A1



AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	



XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A1