




REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2025.08.04	阿树
/	N/A		/	/	/



- Specifications (规格):
- 1.Voltage rating (额定电压): 125V AC/DC
 - 2.Current rating (额定电流): 3A AC/DC
 - 3.Withstanding voltage (耐压值): 1000V AC/minute
 - 4.Insulation resistance (绝缘电阻): ≥1000MΩ
 - 5.Contact resistance (接触电阻): ≤25mΩ
 - 6.Temperature range (使用温度): -40℃~+125℃

PART NO.:
X2009 I F-P SN-B
① ② ③ ④ ⑤ ⑥

- ①Series Number.
②Category: T-terminal
③Category:F-Female Terminal
④Material: P-Phosphor bronze
⑤Plating style:SN-Bright Tin Plating
⑥B:Long style



X2009TF-PSN-B	Phosor Bronze	AWG#22-24	1.40mm(MAX)	Sn-plated	X2009HM-B
PART NO	Material	Wire Range	Insulation O.D.	Finish	Suitable XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树
CHECKED	
APPROVED	

VIEW:
UNIT: mm/in
SIZE: A4

MODEL TYPE: 2.00mm Crimp Style Connectors
PART NO.: X2009TF-PSN-B
DWG NO.: X-X2009TF-PSN-B