



Straight Type




Voltage rating:500V AC/DC
额定电压:500V AC/DC
Current rating:1.0A
额定电流: 1.0A
Insulation resistance:1000MΩ Min
绝缘电阻: 1000MΩ Min
Withstanding voltage:≥500V AC/minute
耐压: ≥500VC/分钟
Temperature range:-40℃-+105℃
使用温度: -40℃-+105℃


X1270 W V -2x06 A2 - 6T V01
① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No.
② Category:W-wafer
③ Welding Board Angle:V- Straight 180°
④ Row No.-Pin No.:2xXX-2x03P~2x40P
⑤ A2:1.27x2.54mm No gaps
⑥ Material:6T-Nylon PA6T UL94V-0
⑦ Planting Category:V01-All Gold Flash

positior	A	B	C
2x03	11.37	9.77	2.54
2x04	12.64	11.04	3.81
2x05	13.91	12.31	5.08
2x06	15.18	13.58	6.35
2x07	16.45	14.85	7.62
2x08	17.72	16.12	8.89
2x09	18.99	17.39	10.16
2x10	20.26	18.66	11.43
2x12	21.53	19.93	12.70
2x13	24.07	22.47	15.24
2x15	26.61	25.01	17.78
2x17	29.15	27.55	20.32
2x20	32.96	31.36	24.13
2x22	35.50	33.90	26.67
2x25	39.31	37.71	30.48
2x30	45.66	44.06	36.83
2x34	50.74	49.14	41.91
2x40	58.36	56.76	49.53



P.C.B Layout



X1270WV-2x06A2-6TV01	PA6T UL 94V-0	Brass	Gold Flash	X1270HA2-06B
				X1270HA2-06A
PART NO	Material	Material(Pin And Solder Tabs)	Finish(Pin And Solder Tabs)	Suitable XKB Housing

					ANGLAR	±5°
Δ x					L≤ 4	±0.2
Δ x					4<L≤ 16	±0.3
Δ x					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE:
DWN		VIEW:	1.27x2.54mmJane cattle简牛
CHKD		UNIT: mm/in	PART NO.:
APPD		SIZE: A4	X1270WV-2x06A2-6TV01
			DWG NO.:
			X-X1270WV-2x06A2-6TV01
		WEIGHT	SHEET
			1/1
		REVISION	A0