

1

2

3

4

REVISIONS

REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.06.06	阿树

SPECIFICATION

Contact Rating: 50mA,12V DC

Contact Resistance: 100mΩ max

Insulation Resistance: 100MΩ min.500V DC

Dielectric Strength: 250V AC/1minute


Travel: 0.20mm

Operating Temp: -30℃~+85℃

Storage Temp: -30℃~+80℃

PAPT NO	TS-1186E-C-A
Operating Force	B:160gf C:260gf
Height	H:3.55
Fixed column	A:With B:Without

⑤	Terminal	2	Brass (0.30t)	Plating silvering
④	Contact	1	F.ag/SUS	Natural
③	Base	1	PA46	
②	Cover	1	Brass	Plating Nickel
①	Keystake	1	PA46	
ITEM	PAPT NAMF	QTY	MATERIAL	FINISHING



Circuit Diagram

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	TACT SWITCH
CHECKED		UNIT:	mm/in	PART NO.:	TS-1186E-C-A
APPROVED		SIZE:	A4	DWG NO.:	TS-1186E-C-A

SCALE	PAGE	REVISION
N/A	1/1	A1

XKB INDUSTRIAL PRECISION CO.,LIMITED

1

2

3

4