

1

2

3

4

A

B

C



D

A




B

C


D



SPECIFICATION
Contact Rating: 50mA,12V DC
Contact Resistance: 100mΩ max
Insulation Resistance: 100MΩ min.500V DC
Dielectric Strength: 250V AC/1minute
Travel: 0.15mm
Operating Temp: -30℃~+85℃
Storage Temp: -30℃~+80℃



P.C.B LAYOUT



PAPT NO	TS-1010B-C-A
Operating Force	A:100gf B:160gf C:260gf
Height	H:3.5
Position Foot	A:With B:without

⑤	Terminal	2	Brass (0.30t)	Plating silvering
④	Contact	1	F.ag/SUS	Natural
③	Base	1	LCP	
②	Cover	1	Brass	Plating Nickel
①	Keystake	1	Pa46	
ITEM	PAPT NAMF	QTY	MATERIAL	FINISHING

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE: TACT SWITCH		
CHECKED		UNIT:	mm/in	PART NO.: TS-1010B-C-A		
APPROVED		SIZE:	A4	DWG NO.: TS-1010B-C-A		
PRECISION CO.,LIMITED				SCALE	PAGE	REVISION
				N/A	1/1	A1

1

2

3

4