





	REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.06.04	阿树

Code—x	H
A	2.5
B	3.1
C	3.4
D	3.7
E	4.3
F	5.0




PCB LATOUT TOP VIEW



SPECIFICATION

Contact Rating:	50mA,12V DC
Contact Resistance:	100m Ω max
Insulation Resistance:	100M Ω min.500V DC
Dielectric Strength:	250V AC/1minute
Travel:	0.25mm
Operating Temp:	-30℃~+85℃
Storage Temp:	-30℃~+80℃

PAPT NO	TS-1157-C-E
Operating Force	A:100gf B:160gf C:260gf
Height	Code-x



AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	

XK13 星城
Connection

DESIGN	阿树	VIEW: 	MODEL TYPE: TACT SWITCH
CHECKED		UNIT: mm/in	PART NO.: TS-1157-C-E
APPROVED		SIZE: A4	DWG NO.: TS-1157-C-E

⑤	Terminal	4	Brass (0.30t)	Plating silvering
④	Contact	1	F.ag/SUS	Natural
③	Base	1	PA46	
②	Cover	1	Brass	Plating Nickel
①	Keystone	1	PA46	
ITEM	PAPT NAMF	QTY	MATERIAL	FINISHING