










Specifications:

规格:

Voltage rating:600V AC/DC

额定电压: 600V AC/DC

Current rating:19A AC/DC

额定电流: 19A AC/DC

Withstanding voltage:5000V AC/minute

耐受电压: 5000V AC/分钟

Temperature range:-40℃~+105℃

温度范围: -40℃~+105℃

Insulation resistance:1000MΩ min

绝缘电阻: 1000MΩ Min

Contact resistance:3.5mΩ Max

接触电阻: 3.5mΩ Max

X9635 H M - 03 - N2
① ② ③ ④ ⑤

1.Series No

2.Category:H-HSG

3.Category:M-Male Housing

4.Row No.Pin No:XX-02~10P

5.Material:N0-Nylon 66 UL94V-0 ;
N2-Nylon 66 UL94V-2 (White)

Poles	Dimensions(mm)	
	A	B
2	13.97	6.35
3	20.32	12.70
4	26.67	19.05
5	33.02	25.40
6	39.37	31.75
8	52.07	44.45
10	64.77	57.15

X9635HM-03-N0	Nylon 66 UL94V-0	X9635W	X9635TF
X9635HM-03-N2	Nylon 66 UL94V-2		
PART NO	Material	Suitable XKB Wafer	Suitable XKB Terminal

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX					ANGLAR ±5°
ΔX					L≤ 4 ±0.2
ΔX					4<L≤ 16 ±0.3
ΔX					16<L≤ 63 ±0.4
MARK					L> 63 ±0.5
REVISIONS					
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn					

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND	SCALE: N/A	MODEL TYPE: 6.35mm Crimp Style Connector
DWN	VIEW:	
CHKD	UNIT: mm/in	PART NO.: X9635HM-03-N2
APPD	SIZE: A4	DWG NO.: X-X9635HM-03-N2
		WEIGHT
		SHEET 1/1
		REVISION A0