



A




SS-12D10 L 4

Knob Type
L
G




H(mm)
2~12

Colour
Blank:Standard Black
R:Red



Typical Specifications

1. Rating: AC 125V 3A
2. Insulation Resistance: 1,000M min
3. Dielectric strength: 1,500V RMS
4. Operating Life: 10,000 cycles



SCHEMA
TIC(NON-SHORTING)

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	

XKLB 星城
Connection

DESIGN	阿树	VIEW:		MODEL TYPE:	SLIDE SWITCH	
CHECKED		UNIT:	mm/in	PART NO.:	SS-12D10L4	
APPROVED		SIZE:	A4	DWG NO.:	X-SS-12D10L4	
PRECISION CO.,LIMITED				SCALE	PAGE	REVISION
				N/A	1/1	A1

1