







REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A			2025.10.13	



P.C.B LAYOUT
(top view)



MATING PLUG
Jack Insertion Depth: 9.0 mm

SCHEMATIC	
Model	DC-026M
Center Pin	Ø2.0 mm Ø2.5 mm

Terminal 3	Phosphor Bronze	Tin
Terminal 2	Brass	Tin
Terminal 1	Brass	Tin
Center pin	Brass	Tin
Plastic	PBT	
Axle sleeve	Brass	Tin
PAPT NAMF	MATERIAL	PLATING

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	
CHECKED	
APPROVED	

VIEW:	
UNIT:	mm/in
SIZE:	A4

MODEL TYPE:	DC POWER JACK
PART NO.:	DC-026M-5A-2.5
DWG NO.:	