





Assembly Layout

Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:1000V AC/minute

耐受电压: 1000V AC/分钟

Temperature range:-25℃~+85℃

温度范围: -25℃~+85℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤30mΩ

接触电阻: ≤30mΩ

After environmental testing:≤40mΩ

环境测试后: ≤40兆欧

X2011 W R S-03 A -9T SN

① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- 1.Series No
- 2.Category:W-WAFER
- 3.Welding Board Angle:R-Right Angle 90°
- 4.Welding Way:S-SMT
- 5.Row No-Pin No:XX-02P~16P
- 6.Plug the Pin&Special N0:
A-With Located Block
- 7.Material:9T:PA9T UL 94V-0
- 8.Plating Category:SN-Bright Tin Plating
- 9.Color:Blank-Natural Color

poles	Dimensions(mm)				poles	Dimensions(mm)			
	A	B	C	D		A	B	C	D
2	8.00	2.00	2.70	4.75	10	24.00	18.00	15.50	20.90
3	10.00	4.00	3.20	6.75	11	26.00	20.00	15.50	22.90
4	12.00	6.00	3.50	8.90	12	28.00	22.00	15.50	24.90
5	14.00	8.00	5.50	10.90	13	30.00	24.00	15.50	26.90
6	16.00	10.00	7.50	12.90	14	32.00	26.00	15.50	28.90
7	18.00	12.00	9.50	14.90	15	34.00	28.00	15.50	30.90
8	20.00	14.00	11.50	16.90	16	36.00	30.00	15.50	32.90
9	22.00	16.00	13.50	18.90					

X2011WRS-03A-9TSN	PA9T UL 94V-0	Brass	Phosphor Bronze	Tin-Plated	X2011H-A
PART NO	Material	Material(pin)	Material(Solder Tab)	Finish(Pin and Solder tab)	Suitable XKB Housing

Wire to board connector

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX					ANGLAR ±5°
ΔX					L≤ 4 ±0.2
ΔX					4<L≤ 16 ±0.3
ΔX					16<L≤ 63 ±0.4
ΔX					L> 63 ±0.5
REVISIONS					UNSPECIFIED TOLERANCES
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn					

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: 2.00mm Crimp Style Connectors
DWN		VIEW:	PART NO.: X2011WRS-03A-9TSN
CHKD		UNIT: mm/in	DWG NO.: X-X2011WRS-03A-9TSN
APPD		SIZE: A4	
			WEIGHT
			SHEET
			REVISION
			1/1
			A0