





Specifications:  
Voltage rating:250V AC/DC  
Current rating:2A AC/DC  
Withstanding voltage:800V AC/minute  
Temperature range:-40℃-+85℃  
Insulation resistance:≥1000MΩ  
Contact resistance:≤20mΩ



X2016 H M - 12 - N0  
① ② ③ ④ ⑤

- 1.Series No
- 2.Category:H-Housing
- 3.M-Male
- 4.Row No.Pin No:XX-02~16P
- 5.Material:N0-PA66 UL 94V-0

| POLES | A     | B     | C     |
|-------|-------|-------|-------|
| 2     | 2.00  | 4.60  | 5.80  |
| 3     | 4.00  | 6.60  | 7.80  |
| 4     | 6.00  | 8.60  | 9.80  |
| 5     | 8.00  | 10.60 | 11.80 |
| 6     | 10.00 | 12.60 | 13.80 |
| 7     | 12.00 | 14.60 | 15.80 |
| 8     | 14.00 | 16.60 | 17.80 |
| 9     | 16.00 | 18.60 | 19.80 |
| 10    | 18.00 | 20.60 | 21.80 |
| 11    | 20.00 | 22.60 | 23.80 |
| 12    | 22.00 | 24.60 | 25.80 |
| 13    | 24.00 | 26.60 | 27.80 |
| 14    | 26.00 | 28.60 | 29.80 |
| 15    | 28.00 | 30.60 | 31.80 |
| 16    | 30.00 | 32.60 | 33.80 |



|               |               |                       |                               |
|---------------|---------------|-----------------------|-------------------------------|
| X2016HM-12-N0 | PA66 UL 94V-0 | X2016TF               | X2016W X2016HF                |
| PARY N0       | Matrial       | Suitable XKB Terminal | Suitable XKB Wafer or Housing |

|      |  |             |                                             |
|------|--|-------------|---------------------------------------------|
| DSND |  | SCALE: N/A  | MODEL TYPE:<br>2.0mm Crimp Style Connectors |
| DWN  |  | VIEW:       | PART NO.:<br>X2016HM-12-N0                  |
| CHKD |  | UNIT: mm/in | DWG NO.:<br>X-X2016HM-12-N0                 |
| APPD |  | SIZE: A4    |                                             |

| MARK                                          | DESCRIPTION | DATE | REVISED | APPROVED | UNSPECIFIED TOLERANCES |
|-----------------------------------------------|-------------|------|---------|----------|------------------------|
| ΔX                                            |             |      |         |          | ANGLAR ±5°             |
| ΔX                                            |             |      |         |          | L≤ 4 ±0.2              |
| ΔX                                            |             |      |         |          | 4<L≤ 16 ±0.3           |
| ΔX                                            |             |      |         |          | 16<L≤ 63 ±0.4          |
| MARK                                          |             |      |         |          | L> 63 ±0.5             |
| REVISIONS                                     |             |      |         |          |                        |
| www.helloxkb.com www.helloxkb.cn www.xk-dg.cn |             |      |         |          |                        |



XKB INDUSTRIAL PRECISION CO.,LIMITED

| WEIGHT | SHEET | REVISION |
|--------|-------|----------|
|        | 1/1   | A0       |