






REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE		
A1	N/A		产品尺寸变更, 图面升级整理图面	2024.08.28	阿树






■SPECIFICATIONS

- Current rating:DC 12V/50mA
- Withstanding Voltage:250V AC/minute
- Insulation resistance:≥100MΩ
- Contact resistance:≤100mΩ
- Operating Force:180±30gf
- Travel:0.20±0.10mm
- Operating life:50,000 Min

PAPT NO	TS-1133-C-A
Operating Force	A:100gf B:160gf C:260gf
Keystone	A:PA46 B:Silica gel



PCB INSTALLATION DIAGRAM



CIRCUIT DIAGRAM

6	Cover	1	Phosphor copper	silver plating
5	Button	1	PPA	Black
4	Waterproof membrane	1	Polyimide film	brown
3	Shrapnel	1	Sus	silver plating
2	Pedestal	1	PPA	Black
1	Pin	1	Phosphor copper	silver plating
NO	NAME	QTY	MATERIAL	Remark

ANGULAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树
CHECKED	
APPROVED	

VIEW:	
UNIT:	mm/in
SIZE:	A4

MODEL TYPE:	TAT SWITCH
PART NO.:	TS-1133-C-A
DWG NO.:	X-TS-1133-C-A

SCALE	PAGE	REVISION
N/A	1/1	A1