


	REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		图面升级整理图面	2025.03.08	阿树
A2	N/A	A2X3	产品尺寸变更	2025.09.15	阿树



Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:1000V AC/minute

耐受电压: 1000V AC/分钟

Temperature range: -40°C-+125°C

温度范围: $-40^{\circ}\text{C}-+125^{\circ}\text{C}$

Insulation resistance:1000MΩ min

绝缘电阻: 1000MΩ M

Contact resistance:20mΩ Max

接触电阻: 20mΩ Max

PART NO.:

X9555 W V-2x06-6T V01

① ② ③ ④ ⑤ ⑥

①Series No



②Category:W—Wafer

③Welding Board Angle:V—Stright 180°


④Row No.Pin No:2xXX-2x05~2x32P

⑤Material:6T-PA9T;

⑥Plating:V01—Gold Flash;



poles	Dimensions(mm)			poles	Dimensions(mm)		
	A	B	C		A	B	C
2x03	5.08	13.22	15.22	2x18	43.18	51.32	53.32
2x04	7.62	15.76	17.76	2x19	45.72	53.86	55.86
2x05	10.16	18.30	20.30	2x20	48.26	56.40	58.40
2x06	12.70	20.84	22.84	2x21	50.80	58.94	60.94
2x07	15.24	23.38	25.38	2x22	53.34	61.48	63.48
2x08	17.78	25.92	27.92	2x23	55.88	64.02	66.02
2x09	20.32	28.46	30.46	2x24	58.42	66.56	68.56
2x10	22.86	31.00	33.00	2x25	60.96	69.10	71.10
2x11	25.40	33.54	35.54	2x26	63.50	71.64	73.64
2x12	27.94	36.08	38.08	2x27	66.04	74.18	76.18
2x13	30.48	38.62	40.62	2x28	68.58	76.72	78.72
2x14	33.02	41.16	43.16	2x29	71.12	79.26	81.26
2x15	35.56	43.70	45.70	2x30	73.66	81.80	83.80
2x16	38.10	46.24	48.24	2x31	76.20	84.34	86.34
2x17	40.64	48.78	50.78	2x32	78.74	86.88	88.88



PCB LAYOUT

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED	TOLERAUCES

XK13 星城
Connection

X9555WV-2x06-6TV01	PA6T UL 94V-0	Brass	Gold-Flash	X9555H1-2xXXX
				X9555H2-2xXXX
				X9555H3-2xXXX
				X9555H4-2xXXX
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB IDC

	DESIGN	阿树	VIEW: 	MODEL TYPE: 2.54mm Jane cattle 简牛
	CHECKED		UNIT: mm/in	PART NO.: X9555WV-2x06-6TV01
	APPROVED		SIZE: A4	DWG NO.: X-X9555WV-2x06-6TV01

AL PRECISION CO.,LIMITED	SCALE	PAGE	REVISION
	N/A	1/1	A2