


1	2	3	4
---	---	---	---



Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2	2.54	5.08	10	22.86	25.4
3	5.08	7.62	11	25.4	27.94
4	7.62	10.16	12	27.94	30.48
5	10.16	12.70	13	30.48	33.02
6	12.70	15.24	14	33.02	35.56
7	15.24	17.78	15	35.56	38.10
8	17.78	20.32			
9	20.32	22.86			

X2510WR-04-N0SN	Nylon 66 94V-0 UL	Brass	Tin-Plated	X2510H
PART NO	Material	Material(Pin)	Finish(Pin)	Mates With XKB Housing

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERAuCES	

XKLB 星城
Connection

DESIGN	阿树	VIEW:	MODEL TYPE: 2.54mm Crimp Style Connector		
CHECKED		UNIT: mm/in	PART NO.: X2510WR-04-N0SN		
APPROVED		SIZE: A4	DWG NO.: X-X2510WR-04-N0SN		
PRECISION CO., LIMITED			SCALE N/A	PAGE 1/1	REVISION A1