





Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:800V AC/minute

耐受电压: 800V AC/分钟

Temperature range:-25℃~+85℃

温度范围: -25℃~+85℃

Insulation resistance:1000MΩ min

绝缘电阻: 1000MΩ Min

Contact resistance:20mΩ Max

接触电阻: 20mΩ Max

X2000 W R S - 05 - 6T SN

① ② ③ ④ ⑤ ⑥ ⑦

1.Series No

2.Category:W-Wafer



3.Welding Board Angle:R-Stright 90°

4.Weding Way:S-SMT


5.Row No.Pin No:XX-02~15P

6.Material:6T-PA6T UL94V-0 Beige


7.Plating:SN-Tin Plated



Schematic Diagram of
10, 11,12,13,14,15-Hole



PCB LAYOUT



Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	2.00	8.00	4.55	09	16.00	22.00	18.55
03	4.00	10.00	6.55	10	18.00	24.00	20.55
04	6.00	12.00	8.55	11	20.00	26.00	22.55
05	8.00	14.00	10.55	12	22.00	28.00	24.55
06	10.00	16.00	12.55	13	24.00	30.00	26.55
07	12.00	18.00	14.55	14	26.00	32.00	28.55
08	14.00	20.00	16.55	15	28.00	34.00	30.55

X2000WRS-05-6TSN	PA6T	Brass	X2000H
PART NO	Material	Material(Pin)	Suitable XKB Housing

					ANGLAR	±5°
ΔX					L≤ 4	±0.2
ΔX					4<L≤ 16	±0.3
ΔX					16<L≤ 63	±0.4
MARK					L> 63	±0.5

REVISIONS					UNSPECIFIED TOLERANCES	
	DESCRIPTION	DATE	REVISED	APPROVED		
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: 2.0mm Crimp Style Connector		
DWN		VIEW: 	PART NO.: X2000WRS-05-6TSN		
CHKD		UNIT: mm/in	DWG NO.: X-X2000WRS-05-6TSN		
APPD		SIZE: A4			
L PRECISION CO.,LIMITED			WEIGHT	SHEET	REVISION
				1/1	A0