

1

2

3

4

A

B

C

D




A

B

C

D

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.08.03	阿树



PART NO.:

X9357 H M-2x09 N2
① ② ③ ④ ⑤

■SPECIFICATIONS

- Voltage rating:600V AC/DC
- Current rating:9A AC/DC
- Withstanding Voltage:1500V AC/minute
- Temperature range:-45°C+125°C
- Insulation resistance:≥1000MΩ
- Contact resistance:≤20mΩ

- ①Series No
- ②Category:H-HSG
- ③Welding Board Angle:M-Male HGS
- ④Row No.-Pin No.:2xXX-2x01P~2x10P,2x12P
- ⑤Material:N2-PA66 94V-2 White

Poles	Dimensions(mm)	
	A	B
2x01		5.40
2x02	4.20	9.60
2x03	8.40	13.80
2x04	12.60	18.00
2x05	16.80	22.20
2x06	21.00	26.40
2x07	25.20	30.60
2x08	29.40	34.80
2x09	33.60	39.00
2x10	37.80	43.20
2x12	46.20	51.60

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCE	



X9357HM-2x09-N2	PA66	X9357W-A	X9357HF
PART NO	Material	Suitable XBK Wafer	Suitable XBK Housing
DESIGN	阿树	VIEW:	MODEL TYPE: 4.20 mm Crimp Style Connector
CHECKED		UNIT: mm/in	PART NO.: X9357HM-2x09-N2
APPROVED		SIZE: A4	DWG NO.: X-X9357HM-2x09-N2
		SCALE	PAGE
		N/A	1/1
		REVISION	A1

1

2

3

4

