


1.View and size(视图及尺寸)

Main technical indicators(主要技术指标)	
1.Mating (插拔次数)	5000
2.Working Temperature (温度)	-55~+150 ℃
3.IP Rating (防护级别)	IP 50
4.Diameter of socket end(插合端直径)	Ø0.7
5.Testing Voltage (测试电压)	850V
6.Working Voltage (工作电压)	700V
7.Rated Current (额定电流)	4.5A
8.Shell material(壳体材质)	Brass (chromium plating)/(nickel plating) fixation ring/ 黄铜 (镀铬) / (镍微) 固定圈
9.Pin Material(插针材料)	Copper alloy gold plating(铜合金镀金)
10.Insulator material(绝缘体材质)	PPS


Sum up(总结)	
Series(系列)	B
Shell style/model (外壳样式/型号)	ZXG Elbow receptacle for printed circuit with two nuts (solder or screw fixing, back panel mounting)/带两个螺母的印刷电路弯头插座, 焊料或螺钉固定, 背板安装
Button (按键)	A button(一个按键)
Termination type (终止类型)	Female print 90°PCB(印刷90° PCB)
Line diameter awg(线材直径)	22AWG-30AWG
Cable diameterΦ (电缆直径)	0-0
Match plug(匹配插头)	TGG.0B.P04.CLAD52H

Location pin combination (定位销组合)				
编号 Number	Number of positioning pins(定位销数量)	Angle(角度)	Series(系列)-0B	
G	One(1)	A	(Zero degrees)0°	
A	Two(2)		Thirty degrees(30°)	
B	Two(2)		Sixty degrees(60°)	
C	Two(2)		Ninety degrees(90°)	
D	Two(2)	β	135 degrees(135°)	
E	Two(2)		145 degrees(145°)	
F	Two(2)		155 degrees(155°)	
J	Two(2)	γ	Forty-five degrees(45°)	
K	Two(2)		Seventy degrees(70°)	
L	Two(2)		80 degrees(80°)	


	A	B	C/√	ANGLE	
5-10	±0.02	±0.05	±0.1	0°-30°	±0.1°
50-100	±0.1	±0.15	±0.2	61°-90°	±0.5°
50-100	±0.15	±0.2	±0.25		
100-	±0.15%	±0.20%	±0.25%		




	A	L	K	C	e	M	H	S2
MM	12	25.0	13.3	12.7	M9°0.6	3.2	2.5	11
in	0.4725	0.9843	0.5236	0.5		0.126	0.0985	0.4331




Pcb plate opening size
(PCB板开孔尺寸)




M-directional layout
(M向排版位)



Boarded mother adhesive core
(板接型母胶芯)



Positive view of the socket
(插座正视图)



DESIGNED(设计)		DATE(日期)		SCALE(比例)	N/A(不适用)	MODEL TYPE 型号类型: ZXG.0B.P04.HLN
CHECKED(校对)		DATE(日期)		VIEW(视图)		PART NO. 0B4-core socket 名称: 0B4芯插座
APPROVED(审核)		DATE(日期)		UNIT(单位)	MM	DWG NO.:
REVISIONS				MATERIAL (材料)		
www.helloxkb.com www.helloxkb.cn				XKB INDUSTRIAL PRECISION CO.,LIMITED		WEIGHT(重量) SHEET(张) REVISION(修订) 1/1 A0