









REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.07.17	阿树



- Specifications
- Voltage rating:250V AC/DC
 - Current rating:5A AC/DC
 - Withstanding voltage:1000V AC/minute
 - Temperature range:-45° to+125°
 - Insulation resistance:≥1000MΩ Min
 - Contact resistance:≤10mΩ Max
 - After environmental testing: ≤20mΩ



PART NO.:

X3025 H F-06 G-N2 XX
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series No
②Category:H-HSG
③Category:F-Female Housing
④Row No.Pin No:XX-02~12Pin
⑤Plug the Pin &Special No.:l-Without Ears
G-With Ears
⑥Material: N2-PA66 94V-2;
⑦Color: Blank-Natural Color; WH-White

1X7PIN		
1X8PIN		1X6PIN
1X9PIN		1X5PIN
1X10PIN		1X4PIN
1X11PIN		1X3PIN
1X12PIN		1X2PIN

Poles	Dimensions (mm)		Poles	Dimensions (mm)	
	A	B		A	B
02	3.00	6.90	08	21.00	24.90
03	6.00	9.90	09	24.00	27.90
04	9.00	12.90	10	27.00	30.90
05	12.00	15.90	11	30.00	33.90
06	15.00	18.90	12	33.00	36.90
07	18.00	21.90			

X3025HF-06G-N2	Nylon 66 94V-2	Natural Color	X3025TM	X3025HM	Withe Ears
X3025HF-XXG-N2WH		White			Without Ears
X3025HF-XXI-N2		Natural Color			
X3025HF-XXI-N2WH		White			
PART NO	Material	Color	Suitable XKB Terminal	Mates With XKB Wafer	Note

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	
CHECKED		UNIT:	mm/in
APPROVED		SIZE:	A4

MODEL TYPE:	3.00mm Crimp Style Connectors
PART NO.:	X3025HF-06G-N2
DWG NO.:	