



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		图面升级整理图面	2025.02.24	阿树
A2	N/A		产品电气性能变更	2025.12.23	阿树


A




B



C



P.C.B LAYOUT



Specifications:
规格:
Voltage rating:500V AC/DC
额定电压: 500V AC/DC
Current rating:2A AC/DC
额定电流: 2A AC/DC
Withstanding voltage:500V AC/minute
耐受电压: 500V AC/分钟
Temperature range:-40℃-+125℃
温度范围: -40℃-+125℃
Insulation resistance:≥1000MΩ
绝缘电阻: ≥1000MΩ
Contact resistance:≤20mΩ
接触电阻: ≤20mΩ
Material:PA6T UL94V-0
材质: PA6T UL94V-0
Plating Category:1U"Gold
镀层: 1U"Gold
Wave soldering temperature:255±5℃, 10S
波峰焊温度: 255±5℃, 10S

PART NO.:

X4611 W R-03 ! U-C40 D50-E12 F12
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩

- ①Series No
- ②Category:W-Wafer
- ③Welding Board Angle:R-Stright 90°
- ④Row No -Pin No:XX-02P-40P
- ⑤Plastic height: l=2.0mm
- ⑥U:U-Type U
- ⑦Plastic height:C=4.0mm
- ⑧Pin Pitch:D=5.0mm
- ⑨Pin length:E=1.25mm
- ⑩Pin length:F=1.25mm

D

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAuces	



DESIGN	阿树	VIEW:	MODEL TYPE:
CHECKED		UNIT: mm/in	PART NO.:
APPROVED		SIZE: A4	DWG NO.:

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A2