





XKB

由 AUTODESK 学生版生成



P.C.B LAYOUT

Specifications:

规格: XKB
Voltage rating:600V AC/DC
额定电压: 600V AC/DC
Current rating:9A AC/DC
额定电流: 9A AC/DC
Withstanding voltage:1500V AC/minute
耐受电压: 1500V AC/分钟
Temperature range:-25℃-+85℃
温度范围: -25℃-+85℃
Insulation resistance:≥1000MΩ
绝缘电阻: ≥1000MΩ
Contact resistance:≤10mΩ
接触电阻: ≤10mΩ
After environmental test:≤20mΩ
环境测试后: ≤20兆欧

X9357 WV X-2x11 HB-N0 SN

- 01 Series No
02 Category:W-wafer
03 Welding Board Angle:V-Straight 180°
04 Welding Way: Blank-DIP
05 Row No.-Pin No: 2*XX-2*02P-2*12P
06 Plug the Pin&Specal NO.:
HB-The hollow needle with positioning column
arrange ushering
07 Material:NO-PA66 94V-0:N2-PA66 94V-7
08 Planting Category:SN-Bright tin plating
09 Color:Blank-Natural Color

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2*02	4.20	15.10	2*08	29.40	40.30
2*03	8.40	19.30	2*09	33.60	44.50
2*04	12.60	23.50	2*10	37.80	48.70
2*05	16.80	27.70	2*11	42.00	52.90
2*06	21.00	31.90	2*12	46.20	57.10
2*07	25.20	36.10			

X9357WV-2x11HB-N0SN	Nylon 66 UL 94V-0	Brass	Tin-Plated	X9357HM-B
X9357WV-2x11HB-N2SN	Nylon 66 UL 94V-2	Brass	Tin-Plated	X9357HM-B
PART N0	Material	Material(Pin)	Finish(Pin)	Suitable XKB Housing

XKB							DSND		DATE		SCALE: N/A	MODEL TYPE:
							DWN		DATE		VIEW: 	2.40mm Crimp Style Connectors
Δx				XKB	ANGLAR	±5°	CHKD		DATE		UNIT: mm/in	PART NO.:
Δx					L≤4	±0.2						X9357WV-2x11HB-N0SN
Δx					4<L≤16	±0.3						
Δx					16<L≤63	±0.4	APPD		DATE		SIZE: A4	DWG NO.:
MARK	DESCRIPTION			DATE	REVISED	APPROVED						L>63
REVISIONS							UNSPECIFIED TOLERANCES					
www.helloxkb.com							XKB INDUSTRIAL PRECISION CO.,LIMITED					
							WEIGHT	SHEET	REVISION			
							1.0g	1/1	A0			