




REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.2.17	阿树

Specifications:
规格:
Voltage rating:30V AC/DC
额定电压: 30V AC/DC
Current rating:0.3A AC/DC
额定电流: 0.3A AC/DC
Withstanding voltage:100V AC/minute
耐受电压: 100V AC/分钟
Temperature range:-35℃~+85℃
温度范围: -35℃~+85℃
Insulation resistance:50MΩ min
绝缘电阻: 50MΩ Min
Contact resistance:90mΩ Max
接触电阻: 90mΩ Max

PART NO.:
X0408 W V S-24 A-LP V01
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

①Series No
②Category:W-Wafer
③Welding Board Angle:V-Stright 180°
④Welding Way: S-SMT
⑤Row No.Pin No:XX-10~100P
⑥Height:A=1.14mm
⑦Material:LP-LCP UL94V-0 Black
⑧Plating:V01-Gold Flash

Poles	Dimensions(mm)		
	A	B	C
10	3.52	1.60	1.00
12	3.92	2.00	
20	5.52	3.60	
24	6.32	4.40	1.20
30	7.52	5.60	1.50
34	8.32	6.40	2.30
40	9.52	7.60	3.20
44	10.32	8.40	
50	11.52	9.60	
60	13.52	11.60	
70	15.52	13.60	
80	17.52	15.60	
90	19.52	17.60	
100	21.52	19.60	

X0408WVS-24A-LPV01	LCP	Phosphor Bronze	X0408WVS
PART NO	Material	Material(Pin)	Suitable XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE: 0.4mm BTB Connector
CHECKED		UNIT: mm/in	PART NO.: X0408WVS-24A-LPV01
APPROVED		SIZE: A4	DWG NO.:

SCALE	PAGE	REVISION
N/A	1/1	A1