





Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:800V AC/minute

耐受电压: 800V AC/分钟

Temperature range:-40℃~+85℃

温度范围: -40℃~+85℃

Insulation resistance:1000MΩ min

绝缘电阻: 1000MΩ Min

Contact resistance:10mΩ Max

接触电阻: 10mΩ Max

X2581 H - 07 - N0



① ② ③ ④

1.Series No

2.Category:H-Housing

3.Row No.Pin No:XX-02~15 Pin

4.Material:N0-PA66 UL94V-0



Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
02	2.50	7.00	09	20.00	24.50
03	5.00	9.50	10	22.50	27.00
04	7.50	12.00	11	25.00	29.50
05	10.00	14.50	12	27.50	32.00
06	12.50	17.00	13	30.00	34.50
07	15.00	19.50	14	32.50	37.00
08	17.50	22.00	15	35.00	39.50

X2581H-07-N0	PA66	X2581W	X2581T
PART NO	Material	Suitable XKB Wafer	Suitable XKB Terminal

}	DSND		SCALE: N/A	MODEL TYPE: 2.5mm Crimp Style Connector		
	DWN		VIEW: 	PART NO.: X2581H-07-N0		
	CHKD		UNIT: mm/in	DWG NO.: X-X2581H-07-N0		
	APPD		SIZE: A4			
L PRECISION CO.,LIMITED				WEIGHT	SHEET	REVISION
					1/1	A0

					ANGULAR	±5°
ΔX					L≤ 4	±0.2
ΔX					4<L≤ 16	±0.3
ΔX					16<L≤ 63	±0.4
MARK					L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED