



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.06.21	阿树





SCHEMATIC (NON-SHORTING)

SS12D07L X X

H(mm)
2~12

Colour
B:Black
R:Red



RATING	0.3A 50V DC
CIRCUIT	1P2T
CONTACT RESISTANCE	100MΩ MAX
TRAVEL	2MM
OPERATING FORCE	250±100gf
OPERATING LIFE	10000

4	Terminal	3	Brass (0.30t)	Ag Plated
3	Base	1	Phenolic Resin	
2	Cover	1	Sus	Natural
1	Keystake	1	Pa66	Black
ITEM	PART NAME	QTY	MATERIAL	FINISHING

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAuCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	SLIDE SWITCH
CHECKED		UNIT:	mm/in	PART NO.:	SS12D07L5B
APPROVED		SIZE:	A4	DWG NO.:	X-SS12D07L5B

SCALE	PAGE	REVISION
N/A	1/1	A1