





REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.2.27	阿树



规格 Specifications:

额定电压 Voltage rating:250VAC/DC.

额定电流 Current rating:1A AC/DC

耐电压 Withstanding voltage:300V AC/minute

温度区间 Temperature range:-40℃to+105℃

绝缘电阻 Insulation resistance:≥500MΩ Min

接触电阻 Contact resistance:≤20MΩ Max

材料 Material: PA6T 94V-0

镀层 Plating Category: 1U"Gold

波峰焊温度 Wave soldering temperature:255±5℃,10s

PART NO.:

X1311 W V-40 J-C18 D27

① ② ③ ④ ⑤ ⑥ ⑦

- ①Series No
- ②Category:W-Water
- ③Welding Board Angle:V-Straight 180°
- ④Row No -Pin No:XX-01P-40P
- ⑤Plastic height: J=1.0mm
- ⑥Plastic length:C=2.7mm
- ⑦Plastic length:D=1.8mm

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



X1311WV-40J-C18D27	PA6T 94V-0	Brass	1U"Gold	X1311F
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Female

DESIGN	阿树	VIEW:	MODEL TYPE: 1.27mm BTB Connector
CHECKED		UNIT: mm/in	PART NO.: X1311WV-40J-C18D27
APPROVED		SIZE: A4	DWG NO.: X-X1311WV-40J-C18D27
XKB INDUSTRIAL PRECISION CO.,LIMITED			SCALE: N/A
			PAGE: 1/1
			REVISION: A1