






PIN	A	B	C	D	E	F	G
04	8.9	3.0	8.5	5.1	5.3	6.00	4.3
05	9.9	4.0	9.5	6.1	6.3		
06	10.9	5.0	10.5	7.1	7.3	5.75	4.1
07	11.9	6.0	11.5	8.1	8.3		
08	12.9	7.0	12.5	9.1	9.3	6.00	4.3
09	13.9	8.0	13.5	10.1	10.3		
10	14.9	9.0	14.5	11.1	11.3	5.75	4.1
11	15.9	10.0	15.5	12.1	12.3		
12	16.9	11.0	16.5	13.1	13.3	6.00	4.3
13	17.9	12.0	17.5	14.1	14.3		
14	18.9	13.0	18.5	15.1	15.3		
15	19.9	14.0	19.5	16.1	16.3		
16	20.9	15.0	20.5	17.1	17.3		
17	21.9	16.0	21.5	18.1	18.3		
18	22.9	17.0	22.5	19.1	19.3		
19	23.9	18.0	23.5	20.1	20.3		
20	24.9	19.0	24.5	21.1	21.3		
21	25.9	20.0	25.5	22.1	22.3		
22	26.9	21.0	26.5	23.1	23.3		
23	27.9	22.0	27.5	24.1	24.3		
24	28.9	23.0	28.5	25.1	25.3		
25	29.9	24.0	29.5	26.1	26.3		
26	30.9	25.0	30.5	27.1	27.3		
27	31.9	26.0	31.5	28.1	28.3		
28	32.9	27.0	32.5	29.1	29.3		
29	33.9	28.0	33.5	30.1	30.3		
30	34.9	29.0	34.5	31.1	31.3		
31	35.9	30.0	35.5	32.1	32.3		
32	36.9	31.0	36.5	33.1	33.3		


邮箱 : hooya89@hooya.hk
 电话 : 0769-82310511-867





COVER OPEN STATE



CABLE INSERT DIM.
SECTION: A-A



CABLE INSERT DIM.
SECTION: A-A



RECOMMENDED FFC SIZE

					TOLERANCE UNLESS SPECIFIED								
					UP TO 5mm:±0.1	ANGULAR	1						
					ABOVE 5mm:±0.2	±1°	NO	DATE	REVISIONS			BY	APPD
4	CONTACTFOOT	PBS	xx	Au/Sn-Plated	TITLE: FPC, 1.0MM				UNIT : MM	ROHS	DWN		
3	METAL	BRASS	2	Sn-Plated	MODEL: 1.0D-FTX-05P-003				SCALE: 1:1	COMPLIANT	CHK'D		
2	BUTTON	LCP(94V-0)	1	WHITE	 DONGGUANG HAORYU ELECTRONICS CO., LTD 东莞市弘皓电子有限公司				APPD				
1	HOUSING	LCP(94V-0)	1	BLACK					PRO.AGL: 		REV :A0		
NO.	PART NAME	MATERIAL	QTY	FINISHING									