




1

2


3

4

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.06.25	阿树



特性
Characteristic
额定范围
Rated range: 0.1A DC12V
绝缘电阻
Insulation resistance: 100MΩ min(DC100V)
耐压强度
Compressive strength: AC100V(50/60Hz foy1 minute)
机械寿命
Mechanical life: 100,000 cycles
操作温度
Operating temperature: -10c~ +60°
操作力度
Operation strength: 80±50gf 250±100gf




PCB LAYOUT



C向a与e



A向a与bcd



B向a与fg

Circuit Diagram

⑤	Contact	1	Phosphor Bronze	Plating silver
④	Base	1	PPA	
③	Spring	1	Sus	
②	Cover	1	Sus	
①	Keystake	1	Nylon	Black
ITEM	PAPT NAMF	QTY	MATERIAL	FINISHING

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	MULTI-FUNCTIONAL SWITCH
CHECKED		UNIT:	mm/in	PART NO.:	TM-1011A
APPROVED		SIZE:	A4	DWG NO.:	X-TM-1011A

SCALE	PAGE	REVISION
N/A	1/1	A1

1

2

3

4