







REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.2.7	阿树



Specifications:
规格:
Voltage rating:50V AC/DC
额定电压: 50V AC/DC
Current rating:1.5A AC/DC
额定电流: 1.5A AC/DC
Withstanding voltage:500V AC/minute
耐受电压: 500V AC/分钟
Temperature range:-40℃~+125℃
温度范围: -40℃~+125℃
Insulation resistance:100MΩ min
绝缘电阻: 100MΩ Min
Contact resistance:20mΩ Max
接触电阻: 20mΩ Max

PART NO.:
X1256 H-08 L-N0 X
① ② ③ ④ ⑤ ⑥
①Series No
②Category:H-HSG
③Row No.Pin No:XX-02~16 Pin
④Special No:L-Front buckle
⑤Material:N0-PA66 UL94V-0
⑥Color:Blank-Black ; W-White



Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
02	1.25	4.50	10	11.25	14.50
03	2.54	5.75	11	12.50	15.75
04	3.75	7.00	12	13.75	17.00
05	5.00	8.25	13	15.00	18.25
06	6.25	9.50	14	16.25	19.50
07	7.50	10.75	16	17.50	19.75
08	8.75	12.00	16	18.75	21.00
09	10.00	13.25	/		

X1256H-08L-N0	PA66	X1256W-L	X1256T-L
PART NO	Material	Suitable XKB Wafer	Suitable XKB Terminal

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE: 1.25mm Crimp Style Connector
CHECKED		UNIT: mm/in	PART NO.: X1256H-08L-N0
APPROVED		SIZE: A4	DWG NO.: X-X1256H-08L-N0

SCALE	PAGE	REVISION
N/A	1/1	A1