




P.C.B. LAYOUT



Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:500V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-40℃--+105℃

温度范围: -40℃--+105℃

Insulation resistance: 1000MΩ min

绝缘电阻: 1000MΩ Min

Contact resistance:20mΩ Max

接触电阻: 20mΩ Max

X2001 W V S - 2x10 B - 6T V01
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

1.Series No

2.Category:W-Wafer

3.Welding Board Angle:V-Stright 180°

4.Welding Way: S-SMT

5.Row No.Pin No: 2xXX-2x03-2x32P

6.Category:B-Have gaps

7.Material:6T-Nylon 6T UL 94V-0

8.Plating:V01-Gold Flash

Poles	Dimensions		Poles	Dimensions	
	A	B		A	B
2x03	4.00	13.30	2x13	24.00	33.30
2x04	6.00	15.30	2x15	28.00	37.30
2x05	8.00	17.30	2x17	32.00	41.30
2x06	10.00	19.30	2x18	34.00	43.30
2x07	12.00	21.30	2x20	38.00	47.30
2x08	14.00	23.30	2x22	42.00	51.30
2x09	16.00	25.30	2x25	48.00	57.30
2x10	18.00	27.30	2x30	58.00	67.30
2x12	20.00	31.30	/		

X2001WVS-2x10B-6TV01	Nylon 6T	Brass	X2001HA3-2x10
PART NO	Material	Material(Pin)	Suitable XKB IDC

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX					ANGULAR ±5°
ΔX					L ≤ 4 ±0.2
ΔX					4 < L ≤ 16 ±0.3
ΔX					16 < L ≤ 63 ±0.4
ΔX					L > 63 ±0.5
REVISIONS					UNSPECIFIED TOLERANCES
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn					

DSND	SCALE: N/A	MODEL TYPE:
DWN	VIEW:	2.0mm Jane cattle 简牛
CHKD	UNIT: mm/in	PART NO.: X2001WVS-2x10B-6TV01
APPD	SIZE: A4	DWG NO.: X-X2001WVS-2x10B-6TV01
XKB INDUSTRIAL PRECISION CO.,LIMITED		WEIGHT
		SHEET 1/1
		REVISION A0