







A



2方4圆



3方5圆



PART NO.:

X9357 H M-2x06 N2
① ② ③ ④ ⑤

■ SPECIFICATIONS

- Voltage rating:600V AC/DC
- Current rating:9A AC/DC
- Withstanding Voltage:1500V AC/minute
- Temperature range:−45°C+125°C
- Insulation resistance:≥1000MΩ
- Contact resistance:≤20mΩ

- ①Series No
②Category:H-HSG
③Welding Board Angle:M-Male HGS
④Row No.-Pin No.:2xXX-2x01P~2x10P,2x12P
⑤Material:N2-PA66 94V-2 White

Poles	Dimensions(mm)	
	A	B
2x01		5.40
2x02	4.20	9.60
2x03	8.40	13.80
2x04	12.60	18.00
2x05	16.80	22.20
2x06	21.00	26.40
2x07	25.20	30.60
2x08	29.40	34.80
2x09	33.60	39.00
2x10	37.80	43.20
2x12	46.20	51.60

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	



X9357HM-2x06-N2		PA66	X9357W-A		X9357HF	
PART NO		Material	Suitable XBK Wafer		Suitable XBK Housing	
	DESIGN	阿树	VIEW: 		MODEL TYPE: 4.20 mm Crimp Style Connector	
	CHECKED		UNIT: mm/in		PART NO.: X9357HM-2x06-N2	
	APPROVED		SIZE: A4		DWG NO.: X-X9357HM-2x06-N2	
PRECISION CO., LIMITED					SCALE N/A	PAGE 1/1
					REVISION A1	

rs

