






Specifications:
 规格:
 Voltage rating:600V AC/DC
 额定电压: 600V AC/DC
 Current rating:23A AC/DC
 额定电流: 23A AC/DC
 Withstanding voltage:2200V AC/minute
 耐受电压: 2200V AC/分钟
 Temperature range:-40℃-+105℃
 温度范围: -40℃-+105℃
 Insulation resistance:1000MΩ min
 绝缘电阻: 1000MΩ Min
 Contact resistance:10mΩ Max
 接触电阻: 10mΩ Max

X5701 H - 03 - N0
 ① ② ③ ④

- 1.Series No
- 2.Category:H-HSG
- 3.Row No.Pin No:XX-02~08P
- 4.Material:N0-Nylon 66 UL94V-0 Black

Poles	Dimensions(mm)	
	A	B
2	5.70	12.05
3	11.40	17.75
4	17.10	23.45
5	22.80	29.15
6	28.50	34.85
7	34.20	40.55
8	39.90	26.25

X5701H-03-N0	Nylon 66	X5701W	X5701H
PART NO	Material	Suitable XKB Wafer	Suitable XKB Housing

DSND	SCALE: N/A	MODEL TYPE: 5.7mm Crimp Style Connector
DWN	VIEW:	PART NO.: X5701H-03-N0
CHKD	UNIT: mm/in	DWG NO.: X-X5701H-03-N0
APPD	SIZE: A4	

					ANGLAR	±5°
Δx					L≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0