




P . C . B . Layout

Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:1000V

AC/minute

耐受电压: 1000V AC/分钟

Temperature range:-40℃-+85℃

温度范围: -40℃-+85℃

Insulation resistance: 1000MΩ min

绝缘电阻: 1000MΩ Min

Contact resistance:20mΩ Max

接触电阻: 20mΩ Max

X8821 W V - 04 H2 - 46 SN

① ② ③ ④ ⑤ ⑥ ⑦

1.Series No

2.Category:W-Wafer

3.Welding Board Angle:V-Stright 180°

4.Row No.Pin No:XX-02Pin-20Pin

5.H2:Horse Hooves

6.Material:46-PA46 UL 94V-0

7.Plating:SN-Bright Tin Plating

Poles	A	B	Poles	A	B
02	2.50	7.50	12	27.50	32.50
03	5.00	10.00	13	30.00	35.00
04	7.50	12.50	14	32.50	37.50
05	10.00	15.00	15	35.00	40.00
06	12.50	17.50	16	37.50	42.50
07	15.00	20.00	17	40.00	45.00
08	17.50	22.50	18	42.50	47.50
09	20.00	25.00	19	45.00	50.00
10	22.50	27.50	20	47.50	52.50
11	25.00	30.00	/		

X8821WV-04H2-46SN	PA46 UL 94V-0	Brass (Plating Tin)	X8821H	X8821T
PART NO	Material	Material(Pin)	Suitabke XKB Housing	Suitabke XKB Terminal

DSND	SCALE: N/A	MODEL TYPE:
DWN	VIEW:	2.5mm Crimp Style Connector
CHKD	UNIT: mm/in	PART NO.:
APPD	SIZE: A4	X8821WV-04H2-46SN
		DWG NO.:
		X-X8821WV-04H2-46SN
		WEIGHT
		SHEET
		REVISION
		1/1
		A0

					ANGULAR	±5°
ΔX					L≤ 4	±0.2
ΔX					4<L≤ 16	±0.3
ΔX					16<L≤ 63	±0.4
MARK					L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED