








2x09PIN以上.



2x02~2x08PIN



PCB LAYOUT

Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:1000V

AC/minute

耐受电压: 1000V AC/分钟

Temperature range:-40°C-+125°C

温度范围: -40℃-+125℃

Insulation resistance:1000MΩ min

绝缘电阻: 1000MΩ Min

Contact resistance:20mΩ Max

接觸電阻: 20mΩ Max

X2508 W V - 2x05 A - N0 SN
 (1) (2) (3) (4) (5) (6) (7)

1.Series No

2.Category:W-Wafer

3.Welding Board Range:V-Stright 180°

4.Row No.Pin No:2xXX-2x02~2x20 Pin

5.Special No.

6. Material: N0-Nylon 66 UL94V-0

7. Plating: SN-Plated Tin

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
2x02	2.50	10.00	6.40	2x10	22.50	30.00	26.40
2x03	5.00	12.50	8.90	2x11	25.00	32.50	28.90
2x04	7.50	15.00	11.40	2x12	27.50	35.00	31.40
2x05	10.00	17.50	13.90	2x13	30.00	37.50	33.90
2x06	12.50	20.00	16.40	2x14	32.50	40.00	36.40
2x07	15.00	22.50	18.90	2x15	35.00	42.50	38.90
2x08	17.50	25.00	21.40	...	...	...	...
2x09	20.00	27.50	23.90	2x20	47.50	55.00	51.40

X2508WV-2x05A-N0SN	Nylon 66	Brass	X2508H-A
PART NO	Material	Material(Pin)	Suitable XKE Housing

		SCALE: N/A	MODEL TYPE: 2.5mm Crimp Style Connector	
DWN		VIEW: 	PART NO.: X2508WV-2x05A-N0SN	
CHKD		UNIT: mm/in	DWG NO.: X-X2508WV-2x05A-N0SN	
APPD		SIZE: A4		
L. PRECISION CO., LIMITED			WEIGHT	SHEET 1/1
				REVISION A0

					ANGLAR	±5°
ΔX					L ≤ 4	±0.2
ΔX					4 < L ≤ 16	±0.3
ΔX					16 < L ≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-da.cn						

XKLE

XKB INDUSTRIAL PRECISION CO.,LIMITED