





| REVISIONS |         |          |                 |            |        |
|-----------|---------|----------|-----------------|------------|--------|
| REV.      | ECN NO. | LOCATION | DESCRIPTION     | DATE       | DESIGN |
| A0        | N/A     |          | INITIAL RELEASE | /          | /      |
| A1        | N/A     |          | 图面升级整理图面        | 2024.08.06 | 阿树     |



- SPECIFICATIONS
- Voltage rating:600V AC/DC
  - Current rating:9A AC/DC
  - Withstanding Voltage:1500V AC/minute
  - Temperature range:−45°C+125°C
  - Insulation resistance:≥1000MΩ
  - Contact resistance:≤10mΩ
  - After environmental testing:≤20mΩ
  - Color:White

PART NO.:  
X9357 W V-2x08-N0 SN  
① ② ③ ④ ⑤ ⑥

- ①Series No  
②Category:W-Wafer  
③Welding Board Angle:V-Straight 180°  
④Row No-Pin No: 2xXX-2x01P~2x12P  
⑤Material: N0-PA66 94V-0;  
N2-PA66 94V-2  
⑥Plating Category: SN-Bright Tin Plating  
V01-Plating Gold Flash



| Poles | Dimensions(mm) |       | Poles | Dimensions(mm) |       |
|-------|----------------|-------|-------|----------------|-------|
|       | A              | B     |       | A              | B     |
| 2x01  | 5.40           | —     | 2x07  | 30.60          | 25.20 |
| 2x02  | 9.60           | 4.20  | 2x08  | 34.80          | 29.40 |
| 2x03  | 13.80          | 8.40  | 2x09  | 39.00          | 33.60 |
| 2x04  | 18.00          | 12.60 | 2x10  | 43.20          | 37.80 |
| 2x05  | 22.20          | 16.80 | 2x11  | 47.40          | 42.00 |
| 2x06  | 26.40          | 21.00 | 2x12  | 51.60          | 46.20 |

|                   |              |               |                      |
|-------------------|--------------|---------------|----------------------|
| X9357WV-2x08-N0SN | PA66 UL94V-2 | Brass         | X9357HM              |
| PART NO           | Material     | Material(Pin) | Suitable XKB Housing |

|                        |       |
|------------------------|-------|
| AuGLAR                 | ±5°   |
| X.                     | ±0.40 |
| X.x                    | ±0.30 |
| X.xx                   | ±0.20 |
| X.xxx                  | ±0.15 |
| UNSPECIFIED TOLERANCES |       |



|          |    |             |                                               |
|----------|----|-------------|-----------------------------------------------|
| DESIGN   | 阿树 | VIEW:       | MODEL TYPE:<br>4.20 mm Crimp Style Connectors |
| CHECKED  |    | UNIT: mm/in | PART NO.:<br>X9357WV-2x08-N0SN                |
| APPROVED |    | SIZE: A4    | DWG NO.:<br>X-X9357WV-2x08-N0SN               |

| SCALE | PAGE | REVISION |
|-------|------|----------|
| N/A   | 1/1  | A1       |