






02P~04P Single Hole
Scale 1:0.7



Specifications:

规格:

1.Voltage rating:150VAC/DC

额定电压: 150V AC/DC

2.Current rating:3A AC/DC

额定电流: 3 A AC/DC

3.Withstanding voltage:500V AC/minute

耐受电压: 500V AC/ 分钟

4.Temperature range: -25 ℃ -+85℃

温度范围: -25℃ -+85℃

5.Insulation resistance:1000MΩ

绝缘电阻: 1000MΩ

6.Contact resistance:20mΩ

接触电阻: 20mΩ

7.After environmental testing:40mΩ

环境测试后: 40 mΩ

X1503 WRS-03 -4TV01
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ① Series No.
- ② Category:W-Water
- ③ Welding Board Angle:R-Straight 90°
- ④ Welding Way S-SMT
- ⑤ Row No -Pin No:XX-02P-12P
- ⑥ Plug the pin&special No
- ⑦ Material:4T PA4T 94V-0
- ⑧ Planting style:V01-Gold-Flash

Poles	Dimensions(mm)			
	A	B	C	D
02	1.50	6.75	2.85	
03	3.00	8.25	4.35	
04	4.50	9.75	5.85	
05	6.00	11.25	7.35	3.00
06	7.50	12.75	8.85	3.00
07	9.00	14.25	10.35	4.50
08	10.50	15.75	11.85	6.00
09	12.00	17.25	13.35	7.50
10	13.50	18.75	14.85	9.00
11	15.00	20.25	16.35	10.50
12	16.50	21.75	17.85	12.00

X1503WRS-03-4TV01	PA4T UL94V-0	Brass	Gold-Flash	Brass	Tin	X1503H
PART NO	Material	Material(Pin)	Finish(Pin)	Material Solder Tabs)	Finish Solder Tabs)	Suitable XKB Housing

DSND		SCALE: N/A	MODEL TYPE: Wire to Board Connector
DWN		VIEW:	PART NO.: X1503WRS-03-4TV01
CHKD		UNIT: mm/in	DWG NO.: X-X1503WRS-03-4TV01
APPD		SIZE: A4	

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX					ANGLAR ±5°
ΔX					L ≤ 4 ±0.2
ΔX					4 < L ≤ 16 ±0.3
ΔX					16 < L ≤ 63 ±0.4
ΔX					L > 63 ±0.5
REVISIONS					
www.helloxkb.com	www.helloxkb.cn	www.xk-dg.cn			

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0