





Y型端子



14P-64P 双槽




Specifications:
规格:
Voltage rating:250V AC/DC
额定电压: 250V AC/DC
Current rating:1A AC/DC
额定电流: 1A AC/DC
Withstanding voltage:1000V AC/minute
耐受电压: 500V AC/分钟
Temperature range:-40℃~+105℃
温度范围: -40℃~+105℃
Insulation resistance:≥1000MΩ
绝缘电阻: ≥1000MΩ
Contact resistance:≤20mΩ MAX
接触电阻: ≤20mΩ MAX

X9555 H1 -2x08 - PT V01
① ② ③ ④ ⑤ ⑥

- 1.Series No
- 2.Category:H1-two-piece HSG
- 3.Row No-Pin No:2xXX-2x03P~2x32P
- 4.Special:NO:X Type A or Type B and Type C
Blank-conventional product
- 5.Material:PT-PBT UL94V-0
- 6.Plating:V01-Gold Flash

X9555H1-2x08-PTV01	PBT	BRASS	Gold Flash	X9555WV-2xXX	XPD1.27-A28PXX-IDC	X9555H-2xXXA
				X9555WR-2xXX		X9555H-2xXXB
				X9555WVS-2xXX		X9555H-2xXXC
				X9555WV-2xXX		X9555H-2xXXA
X9555H1-2x08-PTV01				X9555WR-2xXX		X9555H-2xXXB
				X9555WVS-2xXX		X9555H-2xXXC
PART NO	Material	Material(pin)	Finish(pin)	Suitable XKB Water	Suitable XKB flat cable	Suitable XKB DIP



6P 小鼻/无槽

TYPE C

6P 大鼻/无槽

TYPE A

8P 大鼻/无槽

TYPE A

6P 小鼻/单槽

TYPE B

8P 小鼻/单槽

TYPE B

10P-12P 单槽

Blank

NUMBER OF POSITIONS	DIMENSION			NUMBER OF POSITIONS	DIMENSION		
	A	B	C		A	B	C
2x03	12.32	5.08	1.9	2x13	37.72	30.48	3.8
2x04	14.86	7.62	小1.9/大3.8	2x15	42.80	35.56	3.8
2x05	17.40	10.16	3.8	2x17	47.88	40.64	3.8
2x06	19.94	12.70	3.8	2x18	50.42	43.18	3.8
2x07	22.48	15.24	3.8	2x20	55.50	48.26	3.8
2x08	25.02	17.78	3.8	2x22	60.58	53.34	3.8
2x09	27.56	20.32	3.8	2x25	68.20	60.96	3.8
2x10	30.10	22.86	3.8	2x30	80.90	73.66	3.8
2x11	32.64	25.40	3.8	2x32	85.98	78.74	3.8
2x12	35.18	27.94	3.8				

					ANGLAR	±5°
Δx					L≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						



XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: 2.54mm IDC		
DWN		VIEW:	PART NO.: X9555H1-2x08-PTV01		
CHKD		UNIT: mm/in	DWG NO.: X-X9555H1-2x08-PTV01		
APPD		SIZE: A4	WEIGHT	SHEET 1/1	REVISION A0