








Specifications:
规格:
Voltage rating:250V AC/DC
额定电压: 250V AC/DC
Current rating:4A AC/DC
额定电流: 4A AC/DC
Withstanding voltage:1500V AC/minute
耐受电压: 1500V AC/分钟
Temperature range:-40℃-+105℃
温度范围: -40℃-+105℃
Insulation resistance:1000MΩ min
绝缘电阻: 1000MΩ Min
Contact resistance:15mΩ Max
接触电阻: 15mΩ Max



X2513	W	V	2x08	A	LP	SN
①	②	③	④	⑤	⑥	⑦

- 1.Series No
- 2.Category:W-Wafer
- 3.Welding Board Range:V-Stright 180°
- 4.Row No.Pin No:2xXX-2x02~2x08 Pin
- 5.Special No: A: A Key(Black);
B: B Key (Natural)
- 6.Material:LP-LCP UL94V-0
- 7.Plating:SN-Tin plated

Circuit	DIM. A	DIM. B
N(N=4~16)	1.25 x N - 2.5	1.25 x N + 0.94

X2513WV-2x08A-LPSN	LCP	Copper Alloy	X2513H
X2513WV-2x08B-LPSN			
PART NO	Material	Material(Pin)	Suitable XKB Housing

					ANGLAR	±5°
Δx					L≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						



XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: 2.5mm Crimp Style Connector		
DWN		VIEW:	PART NO.: X2513WV-2x08A-LPSN		
CHKD		UNIT: mm/in	DWG NO.: X-X2513WV-2x08A-LPSN		
APPD		SIZE: A4			
			WEIGHT	SHEET 1/1	REVISION A0