





	REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.2.17	阿树



Specifications:
规格:
Voltage rating: 30V AC/DC
额定电压: 30V AC/DC
Current rating: 3A AC/DC
额定电流: 3A AC/DC
Withstanding voltage: 100V AC/minute
耐受电压: 100V AC/分钟
Temperature range: -35°C - +85°C
温度范围: -35°C - +85°C
Insulation resistance: 50MΩ min
绝缘电阻: 50MΩ Min
Contact resistance: 90mΩ Max
接触电阻: 90mΩ Max



PART NO.:

X3500 W V S-50 A-LP V01
 (1) (2) (3) (4) (5) (6) (7) (8)