

1




2

3



4

REVISIONS

REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.06.18	阿树




P.C.B LAND DIMENSION



SPECIFICATION
1.Rating:DC 12V 50mA Max
2.Contact resistance: 100mΩ MAX
3.Insulation resistance: 100MΩ Min
4.Dielectric strength: 250VAC/min
5.Operating force: 180gf±50gf
6.Operating life: 100,000 cycles

PAPT NO	TS-1186D-C-A
Operating Force	B:160gf C:260gf
Height	H:4.5
Fixed column	A:With B:Without



CIRCUIT DIAGRAM

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN

阿树

VIEW:



MODEL TYPE:

TACT SWITCH

CHECKED

UNIT: mm/in

PART NO.:

TS-1186D-C-A

APPROVED

SIZE: A4

DWG NO.:

TS-1186D-C-A

SCALE

PAGE

REVISION

N/A

1/1

A1

XKB INDUSTRIAL PRECISION CO.,LIMITED

www.helloxkb.com

www.helloxkb.cn

www.xk-dg.cn

1

2

3

4