







■ Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 800V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: $\geq 1000M\Omega$
- Contact resistance: $\leq 20m\Omega$
- After environmental testing : $\leq 20m\Omega$

X2000 W R-10 A- PT SN

① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No.
- ② Category : W-WAFER
- ③ Wedging Board Angle : R-Stright 90°
- ④ Row No.-Pin No.: XX-02P~16P
- ⑤ Plug the Pin & Special NO.:A-With Kink
- ⑥ Material : PT-PBT 94V-0
- ⑦ Plating Category: Sn-Bright Tin Plating

Poles	Dimensions (mm)		Poles	Dimensions (mm)	
	A	B		A	B
02	2.00	6.00	10	18.00	22.00
03	4.00	8.00	11	20.00	24.00
04	6.00	10.00	12	22.00	26.00
05	8.00	12.00			
06	10.00	14.00			
07	12.00	16.00			
08	14.00	18.00			
09	16.00	20.00			

X2000WR-10A-PTSN	PBT UL 94V-0	Brass	Tin-Plated	X2000H
PART NO	Material	Material(pin)	Finish(pin)	Suitable XKB Housing

							DSND		DATE		SCALE: N/A	MODEL TYPE:			
							DWN		DATE		VIEW: 	2.0mm Crimp Style Connectors			
Δx						ANGULAR	±5°	CHKD		DATE		UNIT: mm/in	PART NO.: X2000WR-10A-PTSN		
Δx						L ≤ 4	±0.2								
Δx						4<L ≤ 16	±0.3								
Δx						16<L ≤ 63	±0.4	APPD		DATE		SIZE: A4	DWG NO.: X-X2000WR-10A-PTSN		
MARK	DESCRIPTION					DATE	REVISED								
REVISIONS							UNSPECIFIED TOLERANCES								
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn															
							XKB INDUSTRIAL PRECISION CO.,LIMITED						WEIGHT	SHEET	REVISION
													1.0g	1/1	A0