







Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 800V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: $\geq 1000M\Omega$
- Contact resistance: $\leq 10m\Omega$
- After environmental testing : $\leq 20m\Omega$




X8826 W V-2x05- N0 SN


① ② ③ ④ ⑤ ⑥

- ① Series No.
② Category : W-WAFER
③ Wedding Board Angle : V-Stright 180°
④ Row No.-Pin No.: 2*XX-Double Row
⑤ Material : N0-PA66 94V-0
⑥ Plating Category: Sn-Bright Tin Plating(70u")

Poles	Dimensions(mm)	
	A	B
02	2.50	7.50
03	5.00	10.00
04	7.50	12.50
05	10.00	15.00
06	12.50	17.50
07	15.00	20.00
08	17.50	22.50
09	20.00	25.00
10	22.50	27.50
11	25.00	30.00
12	27.50	32.50
13	30.00	35.00
14	32.50	37.50
15	35.00	40.00
16	37.50	42.50
17	40.00	45.00
18	42.50	47.50
19	45.00	50.00
20	47.50	52.50



CONTACT NO.1



X8826WV-2x05-N0SN	Nyoln 66 UL 94V-0	Brass	Tin-Plated	X8826H
PART NO	Material	Material(pin)	Finish(pin)	Suitable XKB Housing

							DSND		DATE		SCALE: N/A	MODEL TYPE: 2.5mm Crimp Style Connectors					
Δx						ANGLAR		DWN		DATE		VIEW: 	PART NO.:				
Δx						L ≤ 4	±5°						X8826WV-2x05-N0SN				
Δx						4<L ≤ 16	±0.2	CHKD		DATE		UNIT: mm/in	DWG NO.:				
Δx						16<L ≤ 63	±0.3						X8826WV-2x05-N0SN				
MARK	DESCRIPTION				DATE	REVISED	APPROVED	APPD		DATE		SIZE: A4					
REVISIONS																	
							UNSPECIFIED TOLERANCES		XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT		SHEET		REVISION	
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn												1.0g		1/1		A0	