

| REVISIONS |         |          |                 |            |        |
|-----------|---------|----------|-----------------|------------|--------|
| REV.      | ECN NO. | LOCATION | DESCRIPTION     | DATE       | DESIGN |
| A0        | N/A     |          | INITIAL RELEASE | 2024.05.09 |        |
|           |         |          |                 |            |        |


规格 Specification:

- 1.额定值 Rating:8A 125/250VAC  
2.接触电阻 Contact resistance:≤30 mΩ  
3.绝缘电阻 Insulation resistance:≥100 MΩ(DC500V/Min)  
4.电气寿命 Electronics life:>10000 cycles  
5.操作力 Operation force:500±200gf  
6.所有材料符合Rohs要求 All materials are Rohs compliant

PART NO.:

SS-X 08 22 S L-8 R 2 B B  
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪


- ① SS: XKB Vertical handle;  
② Enclosure Material:  
A-Metal case;  
BLANK-Plastic case;  
③ Current Rating: 08-8A;  
④ Switch Circuit:22-2P2T;  
⑤ S: Wire bonding;  
⑥ Handle Shape: L-Flat handle;  
⑦ Handle Height: 3~15mm;  
⑧ Enclosure Shape:R-Locking rings enclosure;  
⑨ Terminal specs:  
1:TYPE-1; 2:TYPE-2; 3:TYPE-3;  
⑩ Handle Colour:  
B-Black; W-White; R-Red  
⑪ Housing Colour:  
B-Black; W-White; R-Red



**XKLB** <sup>®</sup> **US**  
SS Series  
8A 125/250VAC

产品字码标识

|                        |       |
|------------------------|-------|
| ANGULAR                | ±5°   |
| X.                     | ±0.40 |
| X.x                    | ±0.30 |
| X.xx                   | ±0.20 |
| X.xxx                  | ±0.15 |
| UNSPECIFIED TOLERANCES |       |



XKB INDUSTRIAL PRECISION CO.,LIMITED

|          |     |       |       |             |                   |
|----------|-----|-------|-------|-------------|-------------------|
| DESIGN   | 桑 葚 | VIEW: |       | MODEL TYPE: | SLIDE SWITCH      |
| CHECKED  |     | UNIT: | mm/in | PART NO.:   | SS-0822SL-8R2BB   |
| APPROVED |     | SIZE: | A4    | DWG NO.:    | X-SS-0822SL-8R2BB |
|          |     | SCALE | PAGE  | REVISION    |                   |
|          |     | N/A   | 1/1   | A0          |                   |