





REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.1.16	阿树



- NOTES 注释:
- MATERIAL材料:
 - HOUSING外壳: THERMOPLASTIC, HIGH TEMP., UL94V-0; COLOR: SEE PART NO..
 - CONTACTS触点: COPPER ALLOY.
 - FINISH饰面:
 - CONTACT触点: SELECTEIVE GOLD PLATING ON CONTACT AREA. 100 μ"MIN. MATTE TIN PLATING ON SOLDER TAILS 50 μ" MIN. NICKEL UNDERPLATING OVERALL.

PART NO.:
X3157 W S-164-9T V30
① ② ③ ④ ⑤ ⑥

- ①Series No
②Category:W-Wafer
③Welding Board Angle : Straddle
④No.of Pins: 36~164 Pin
⑤Plastic material: PA9T /PA46 UL94V-0
⑥Contact Plating:V15-Gold 15u"
V30-Gold 30u"

DIMENSIONS				
POSITION	A±0.25	B±0.20	C±0.20	D±0.20
36	25.00	7.65	6.00	23.00
64	39.00	21.65	20.00	37.00
98	56.00	38.65	37.00	54.00
164	89.00	71.65	70.00	87.00



AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



DESIGN	阿树	VIEW:	MODEL TYPE: /
CHECKED		UNIT: mm/in	PART NO.: X3157WS-164-9TV30
APPROVED		SIZE: A4	DWG NO.: X-X3157WS-164-9TV30

SCALE	PAGE	REVISION
N/A	1/3	A1

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.1.16	阿树



DIMENSIONS					
POSITION	A	E	J	F	"K"
36	6	23	9.5	8.15	B17
64	20	37	23.5	22.15	B17,B31
98	37	54	40.5	39.15	B17,B31,B48
164	70	87	73.5	72.15	B17,B31,B48,B81

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



DESIGN	阿树	VIEW:	MODEL TYPE: /
CHECKED		UNIT: mm/in	PART NO.: X3157WS-164-9TV30
APPROVED		SIZE: A4	DWG NO.: X-X3157WS-164-9TV30
XKB INDUSTRIAL PRECISION CO.,LIMITED			SCALE: N/A
			PAGE: 2/3
			REVISION: A1

1

2


3

4


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.1.16	阿树

A

CAP





B



A

B

DIM "F" ±0.4



DIMENSIONS	
POSITION	F
36	20.4
64	34.4
98	51.4
164	84.4

C

D

ASSEMBLY WITH CAP CONDITION

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW: 	MODEL TYPE: /
CHECKED		UNIT: mm/in	PART NO.: X3157WS-164-9TV30
APPROVED		SIZE: A4	DWG NO.: X-X3157WS-164-9TV30

1

2

3

4