





3 5 7 PCB LAYOUT



#### Specifications:

规格:

Voltage rating:400V AC/DC

额定电压: 400V AC/DC

Current rating:10A AC/DC

额定电流: 10A AC/DC

Withstanding voltage:1800V AC/minute

耐受电压: 1800V AC/分钟

Temperature range:-40℃-+105℃

温度范围: -40℃-+105℃

Insulation resistance:100MΩ min

绝缘电阻: 100MΩ Min

Contact resistance:10mΩ Max

接触电阻: 10mΩ Max

X2513 W V - 03 A S - LP SN

① ② ③ ④ ⑤ ⑥ ⑦ ⑧

1.Series No

2.Category:W-Wafer

3.Welding Board Angle:V-Stright 180°


4.Row No.Pin No:XX-02~08P

5.Specal No:A-A Key(Black);B-B Key(Natura


6.Specal No:S-With Positioning Column

7.Material:LP-LCP 94V-0


8.Plating Category:SN-Bright Tin Plating




2 PIN




3 PIN




4 PIN



5 PIN



6 PIN



7 PIN

| Poles | Dimensions(mm) |       |
|-------|----------------|-------|
|       | A              | B     |
| 02    | 5.94           | 2.50  |
| 03    | 8.44           | 5.00  |
| 04    | 10.94          | 7.50  |
| 05    | 13.44          | 10.00 |
| 06    | 15.94          | 12.50 |
| 07    | 18.44          | 15.00 |
| 08    | 20.94          | 17.50 |

|                   |          |               |                      |
|-------------------|----------|---------------|----------------------|
| X2513WV-03AS-LPSN | LCP      | Brass         | X2513H               |
| PART NO           | Material | Material(Pin) | Suitable XKB Housing |

|      |  |             |                                             |
|------|--|-------------|---------------------------------------------|
| DSND |  | SCALE: N/A  | MODEL TYPE:<br>2.50mm Crimp Style Connector |
| DWN  |  | VIEW:       | PART NO.:<br>X2513WV-03AS-LPSN              |
| CHKD |  | UNIT: mm/in | DWG NO.:<br>X-X2513WV-03AS-LPSN             |
| APPD |  | SIZE: A4    |                                             |

| ΔX   | DESCRIPTION | DATE | REVISED | APPROVED | ANGLAR   | ±5°  |
|------|-------------|------|---------|----------|----------|------|
| ΔX   |             |      |         |          | L≤ 4     | ±0.2 |
| ΔX   |             |      |         |          | 4<L≤ 16  | ±0.3 |
| ΔX   |             |      |         |          | 16<L≤ 63 | ±0.4 |
| MARK |             |      |         |          | L> 63    | ±0.5 |

#### REVISIONS

UNSPECIFIED TOLERANCES

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED

| WEIGHT | SHEET | REVISION |
|--------|-------|----------|
|        | 1/1   | A0       |