






REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.05.19	阿树



Specifications:
1.Voltage rating: 300V AC/ DC
2.Current rating: 1A AC/DC
3.Withstanding voltage: 900V AC/minute
4.Temperature range: -25° ~+85
5.Insulation resistance: 100MΩ Min
6.Contact resistance: 20mΩ Max
7.Material:LCP Beige UL94V-0
PIN Brass Tin-plated

PART NO.:

X5400 W M-02-LP SN
① ② ③ ④ ⑤ ⑥

- ①Series No
②Category:W-Wafer
③Welding Board Angle: M-Male
④Row No.-Pin No.: XX-Single Row
⑤Material: LP-LCP UL94V-0
⑥Plating Category: SN-Tin Plating

X5400WM-02-LPSN	LCP	Brass	Tin-Plating	X5400WF
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE: 5.4mm BTB Style Connectors
CHECKED		UNIT: mm/in	PART NO.: X5400WM-02-LPSN
APPROVED		SIZE: A4	DWG NO.:

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A1