





REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		独立各PIN数图纸, 增加开孔定位尺寸	2024.12.11	阿树
A2	ECN-P-2026010901	③X1	产品尺寸变更	2026.01.09	阿树

PART NO.:

X06 15 F I 7 B 3
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series No
②Pin No.:15PIN
③Welding Board Angle :F-Female
④T: Tradutional
⑤Planting Catogtry:
1:1U 2:2U 3:3U 4:5U 5:15U 6:30U 7:AU Sn
⑥Color:B:Black W:White BL:Blue Y:Yellow G:Green R:Red
⑦1:TYPE-1; 2:TYPE-2; 3:TYPE-3; 4:TYPE-4; 6:TYPE-6

Specifications:
规格:
Current rating:5A AC/DC
额定电流: 5A AC/DC
Voltage rating:500V AC
额定电压: 500V AC
Withstanding voltage:500V AC/MIN
耐受电压: ≥500V AC/分钟
Temperature range:-55℃-+105℃
温度范围: -55℃-+105℃
Insulation resistance:1000MΩMIN
绝缘电阻: ≥1000MΩ
Contact resistance:30mΩMAN
接触电阻:≤30mΩ
Material And FINISHED:
材料和成本:
INSULATOR:PBT+30% GF UL 94V-0
绝缘体: PBT+30% GF UL 94V-0
SHELL: Steel Plated Ni
外壳: 钢 镀镍
CONTACT MATERIAL:Brass
触点材料: 黄铜



AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



铆合方式	TYPE-1: 铆合	TYPE-6: 直铆锁	TYPE-3: 叉锁	TYPE-2: 铆合锁螺丝
图式				

DESIGN	阿树	VIEW:		MODEL TYPE:	D-SUB
CHECKED		UNIT:	mm/in	PART NO.:	X0615FT7B3
APPROVED		SIZE:	A4	DWG NO.:	X-X0615FT7B3

SCALE	PAGE	REVISION
N/A	1/1	A2